Simultaneous Sampling Multifunction DAQ Device





The USB-1616FS features simultaneous sampling of 16 single-ended analog inputs, 8 DIO lines, and a 32-bit event counter

Overview

The USB-1616FS provides 16 simultaneously sampled 16-bit analog inputs with sample rates up to 50 kS/s per channel, continuous throughputs of 150 kS/s, and 32 kilosample bursts up to 200 kS/s. The device also provides one 32-bit counter and 8 digital I/O lines.

The USB-1616FS design features a heavy-duty chassis with integrated mounting slots, ensuring that the device is rugged enough for any DAQ application.

The combination of the USB-1616FS and Measurement Computing DAQ software suite gives you a complete data acquisition solution that will have you taking measurements in minutes. The device is fully USB plug and play. An external power adapter is included.

Analog Input

The USB-1616FS provides 16 single-ended analog inputs. A channel gain queue feature lets users set up a scan list to sample up to 16 different analog input channels at different gains (ranges).

Simultaneous Sampling

Each analog input channel has a dedicated 16-bit A/D converter for true simultaneous sampling of all 16 inputs.

Sample Rates

With hardware paced mode, the maximum throughput rate is 50 kS/s for one channel, or 9.5 kS/s per channel for all channels.

With burst scan mode, the maximum throughput rate is 50 kS/s per channel for one, two, or three channels, and 16.5 kS/s per channel for all 16 channels.

Digital I/O

Eight digital IO lines are independently selectable as input or output. All digital lines are pulled up by default with a $47 \text{ k}\Omega$ resistor.

Features

- 16 single-ended analog inputs
- 16-bit resolution
- Up to 200 kS/s throughput
- Simultaneous sampling
- 8 digital I/O
- 32-bit counter
- Integrated temperature sensor
- USB expansion port for multiunit daisy-chaining
- External power adapter
- Rugged enclosure
- DIN rail or bench mountable

Supported Operating Systems

 Windows® 11/10/8/7/ Vista®XP, 32/64-bit

Counter Input

The 32-bit event counter accepts frequency inputs up to 1 MHz, and increments when the TTL level transitions from low to high.

Trigger Input

The USB-1616FS has an external digital trigger input. The trigger mode is configurable with software for rising (default) or falling edge.

External Clock I/O

A bidirectional SYNC (synchronization) control line can be configured as either input or output.

Configure as an external clock input to externally clock A/D conversions, or as an output to synchronize with a second USB-1616FS and acquire data from 32 channels.

Measurement Computing (508) 946-5100 1 info@mccdag.com mccdag.com

Software




Calibration

USB-1616FS devices are factory-calibrated using a NIST-traceable calibration process. Specifications are guaranteed for one year. For calibration beyond one year, return the device to the factory for recalibration.

Power

The USB-1616FS receives power from the +9 V unregulated power supply that is shipped with the device. Power and USB connectors let you power and control multiple MCC USB Series products from one external power source and one USB port in a daisy chain fashion.



info@mccdaq.com

Software



Software Support

USB-1616FS devices are supported by the software in the table below.

Ready-to-Run Applications

DAQami™



Data acquisition companion software with drag-and-drop interface that is used to acquire, view, and log data, and generate signals. DAQami can be configured to log analog, digital, and counter channels, and to view that data in real-time or post-acquisition on user-configurable displays. Logged data can be exported for use in Excel® or MATLAB®. Windows OS

DAQami is included with the free MCC DAQ Software bundle.

InstaCal™



An interactive installation, configuration, and test utility for MCC hardware. Windows OS InstaCal is included with the free MCC DAQ Software bundle.

<u>TracerDAQ</u>[™] and <u>TracerDAQ Pro</u>



Virtual strip chart, oscilloscope, function generator, and rate generator applications used to generate, acquire, analyze, display, and export data. Supported features may vary by hardware. The Pro version provides enhanced features. Windows OS

TracerDAQ is included with the free MCC DAQ Software bundle.

TracerDAQ Pro is available as a purchased software download.

General-Purpose Programming Support

<u>Universal Library</u>[™] (<u>UL</u>) for Windows



Library for developing applications in C, C++, VB, C# .Net, VB .Net, and Python on Windows.

The UL for Windows is included with the free MCC DAQ Software bundle.

The UL Python API for Windows is available on GitHub (github.com/mccdaq/mcculw).

<u>Linux®</u> <u>driver</u>



Open-source Linux drivers are available for most MCC devices. Example programs are also provided.

Application-Specific Programming Support

<u>ULx for</u> <u>NI LabVIEW</u>™



A comprehensive library of VIs and example programs for NI LabVIEW that is used to develop custom applications that interact with most MCC devices. Windows OS

ULx for NI LabVIEW is included with the free MCC DAQ Software bundle.

DASYLab®



Icon-based data acquisition, graphics, control, and analysis software that allows users to create complex applications in minimal time without text-based programming. Windows OS

DASYLab is available as a purchased software download. An evaluation version is available for $28\ days$.

MATLAB® driver



High-level language and interactive environment for numerical computation, visualization, and programming. The Mathworks Data Acquisition Toolbox™ allows users to acquire data from most MCC PCI and USB devices.

Visit www.MathWorks.com for more information about the Data Acquisition Toolbox.

Specifications



Analog Input A/D converters: 16-bit, SAR type Number of channels: 16 single-ended

Input configuration: Individual A/D per channel

Sampling method: Simultaneous

Absolute maximum input voltage: CHx IN to GND ±15 V max

Input impedance: 100 MΩ, min Input bandwidth (-3 dB): 50 kHz typ **Input leakage current**: ±1 μA typ Input capacitance: 50 pf typ

Offset temperature drift: 15 ppm/°C typ Gain temperature drift: All ranges 35 ppm/°C typ Input ranges: ±10 V, ±5 V, ±2 V, ±1 V; Software selectable

Sampling rate

Scan to PC memory: up to 50 kS/s, software selectable

Burst scan to 32 k sample FIFO: 20 S/s to 50 kS/s, software selectable

Throughput: Software paced; 30 S/s to 500 S/s all channels; system dependant

Scan to PC memory: Refer to the throughput tables below.

Burst scan to 32 k sample FIFO: (200 kS/s)/(# of channels); 50 kS/s max for

Gain queue: Queue list may contain up to 16 unique, consecutive channels paired with any valid range; software configurable

Resolution: 16 bits

No missing codes: 15 bits

Crosstalk

DC - 25 kHz (sine): -80 dB min

Calibration voltages: 0 V, ±0.625 V, ±1.25 V, ±2.5 V, ±5.0 V, software selectable

Calibration voltage accuracy (Note 1): $\pm 0.5\%$ typ, $\pm 1.0\%$ max Temperature sensor range: 0 °C to +70 °C max

Temperature sensor accuracy: ±3 °C typ

Trigger source: External digital; TRIG_IN; software selectable

Single Board Throughput

An integral USB hub allows up to four USB-1616FS devices to be daisy chained and connected to a single USB port on the host computer. We recommend using a 2.0 or higher USB adapter when daisy chaining devices. Data in the following table reflects typical throughput for a single board system.

Single-Board Throughput; Scan to PC Memory		
Number of Input Channels	Per channel throughput (kS/s)	
1	50000	
2	50000	
3	36000	
4	30000	
5	25000	
6	22000	
7	19000	
8	17000	
9	15000	
11	14000	
12	12500	
13	11250	
14	10500	
15	10000	
16	9500	

The throughput rates apply applies to a single board system. Actual rates are system-dependent and may vary.

Multiple board throughput

An integral USB hub allows up to four USB-1616FS devices to be daisy chained and connected to a single USB port on the host computer. Revision F and later are compatible with USB 3.0. Older revisions can be daisy chained from a Revision F device attached to a USB 3.0 adapter. Refer to "Board Revision" below for revision information.

Data transfer over the USB bus is CPU intensive and system dependent. Multiple board performance is limited by an overall aggregate sample rate. The maximum throughput is the number of samples taken per second, regardless of the number of channels sampled or number of devices installed. The maximum sample rate of any one channel is limited to 50 kS/s.

For example, if the maximum throughput is 150,000 S/s, you may sample 20 channels at 7.5 kS/s, 30 channels at 5 kS/s, 40 channels at 3.75 kS/s, and so on.

Board Revision

The board revision may be determined from the part number label on the board that states "193337X-01L", where X is the board revision.

Calibrated Absolute Accuracy		
Range (V)	Accuracy (mV)	
±10	±5.66	
±5	±2.98	
±2	±1.31	
±1	±0.68	

Accuracy components				
Range (V)	% of Reading	Gain Error at FS (mV)	Offset (mV)	
±10	0.04	4.00	1.66	
±5	0.04	2.00	0.98	
±2	0.04	0.80	0.51	
±1	0.04	0.40	0.28	

All values are (±)

Noise Performance				
Range (V)	Typical Counts	LSBrms		
±10	10	1.52		
±5	10	1.52		
±2	11	1.67		
±1	14	2.12		

Noise distribution is determined by gathering 50 k samples with analog inputs tied to ground (AGND) at the user connector. Samples are gathered at the maximum specified sampling rate of 50 kS/s.

Digital I/O

Digital type: CMOS

Number of I/O: 8 (DIO0 through DIO7)

Configuration: Independently configurable for input or output

Digital I/O transfer rate (software paced): System dependent, 33 port reads to 1000 port reads/writes or single bit reads/writes per second, typ

Input high voltage: 2.0 V min, 5.5 V absolute max Input low voltage: 0.8 V max, -0.5 V absolute min Output high voltage (IOH = -2.5 mA): 3.8 V min Output low voltage (IOL = 2.5 mA): 0.7 V max

Power on and reset state: Input Pull up/down configuration

Earlier than Revision F: All pins pulled up to USB VBUS via 47 k Ω resistors (default). Positions are available for pull-down to ground (GND). Hardware selectable via 0Ω resistors is available as a factory option.

Revision F and later: All pins are configurable via jumper W1 to 5 V or ground via 47 kΩ resistors

Refer to the "Board Revision" discussion above for revision information.

Specifications and Ordering



External Trigger

Trigger source: External digital; TRIG_IN; Schmitt trigger protected with 1.5 k Ω

Trigger mode: Edge sensitive; software selectable for rising (default) or falling edge.

Trigger latency: 10 µs max Trigger pulse width: 1 µs min Earlier than Revision F

Input type: Schmitt trigger, 1.5 k Ω series resistor Input high voltage: 4.0 V min, 5.5 V absolute max Input low voltage: 1.0 V max, -0.5 V min

Input leakage current: ±1.0 µA

Revision F and later

Input type: Schmitt trigger, 47 k Ω pull-down to ground and 1.5 k Ω series

resistor

Schmitt trigger hysteresis: 0.6 V min, 1.5 V max Input high voltage threshold: 3.1 V max Input low voltage threshold: 1.0 V min

Refer to the "Board Revision" on page 4 for revision information.

External Clock I/O

Pin name: SYNC; Schmitt trigger over-current protected with a 200 Ω series resistor.

Pin type: Bidirectional

Software selectable direction

Output: Outputs internal A/D pacer clock

Input: Receives A/D pacer clock from external source. Rising edge sensitive.

Input clock rate: 50 kHz, max

Clock pulse width Input: 1 µs min
Output: 5 µs min

Earlier than Revision F

Input type: Schmitt trigger with 200 Ω series resistor

Input/output resistance: 200 Ω series resistor

Input leakage current: ±1.0 µA

Input high voltage: 4.0 V min, 5.5 V absolute max

Input low voltage: 1.0 V max, -0.5 V absolute min

Output high voltage

IOH = -2.5 mA: 3.3 V min No load: 3.8 V min

Output low voltage

IOL = 2.5 mA: 1.1 V max

No load: 0.6 V max

Revisions F and later

Input type: Schmitt trigger

Input/output resistance: 200 Ω series resistor on output driver; 1.5 kΩ series

resistor on input buffer; 47 k Ω pull-down resistor to ground

Schmitt trigger hysteresis: 0.6 V min, 1.5 V max Input high voltage threshold: 3.1 V max

Input low voltage threshold: 1.0 V min

Output high voltage

IOH = -8 mA: 3.8 V minNo load: 4.4 V min

Output low voltage

IOH = 8 mA: 0.44 V max

No load: 0.1 V max

Refer to the "Board Revision" on page 4 for revision information.

Counter

Pin name: CTR

Counter typ: Event counter Number of channels: 1

Resolution: 32 bits

Maximum input frequency: 1 MHz High pulse width: 500 ns min Low pulse width: 500 ns min

Counter/timer read/write rates (software paced)

Counter read: system dependent, 33 reads to 1,000 reads per second Counter clear: system dependent, 33 reads to 1,000 writes per second Input low voltage limit: 0 V recommended min, -0.5 V absolute min Input high voltage limit: 5.0 V recommended max, 5.5 V absolute max

Earlier than Revision F

Input type: Schmitt trigger, rising edge triggered, 1.5 k Ω series resistor Schmitt trigger hysteresis: 20 mV to 100 mV

Input leakage current: ±1.0 µA

Input high voltage threshold: 1.0 V min

Input low voltage threshold: 4.0 V max

Revision F and later

Input type: Schmitt trigger, rising edge triggered, 1.5 k Ω series resistor, 47 k Ω

pull-down to ground

Schmitt trigger hysteresis: 0.6 V min, 1.5 V max Input high voltage threshold: 3.1 V max

Input low voltage threshold: 1.0 V min

Refer to the "Board Revision" on page 4 for revision information.

Power

Supply current

Continuous mode: 350 mA typ; includes up to 10 mA for the status LEDs User +5V output voltage: 4.0 V min, 5.25 V max; available at the 5V screw terminal;

assumes input power supply voltage is within specified limits

User +5V output current: 50 mA max; available at the 5V screw terminal

USB +5V (VBUS) input voltage: 4.75 V min to 5.25 V max

External Power

External power adapter (included): CB-PWR-9V3A; +9 V ±10%, @ 3 A. If the limit is exceeded, the PWR LED turns off, indicating a power fault condition.

External power input: +6.0 VDC to 12.5 VDC; 9 VDC power supply included. Voltage supervisor limits - PWR LED:

6.0 V > Vext or Vext > 12.5 V: PWR LED = Off (power fault)

6.0 V < Vext < 12.5 V: PWR LED = On

External power output – current range: 4.0 A max. The voltage drop between power input and daisy chain power output is 0.5 V max. Users must plan for this drop to ensure that the last device in the chain will receive at least 6.0 VDC. A user-supplied custom cable is required to daisy chain multiple devices.

Environmental

Operating temperature range: 0 ° C to 70 ° C Storage temperature range: -40 ° C to 85 ° C

Humidity: 0% to 90% non-condensing

Mechanical

Card dimensions (L \times W \times H): 203.2 \times 121.9 \times 20.0 mm (8.0 \times 4.8 \times 0.8 in.) Enclosure dimensions (L \times W \times H): 241.3 \times 125.7 \times 58.9 mm (9.50 \times 4.95 \times 2.32 in.)

USB Specifications

USB device type: USB 2.0 (full-speed) USB compatibility: USB 3.0, 2.0, 1.1

Order Information

Hardware

CB-PWR-9V3A

Part No. Description

USB-1616FS Multifunction USB DAQ device with simultaneous

sampling, 16-bit analog inputs, 200 kS/s sampling, 32-bit

event counter, and 8 digital I/O lines. 9 volt replacement power supply.

DASYLab

Part No. Description

TracerDAQ Pro Out-of-the-box virtual instrument suite with strip chart,

oscilloscope, function generator, and rate generator professional version

Software also Available from MCC

Icon-based data acquisition, graphics, control, and analysis